



THE NEXT GENERATION CO2

analyzer for beverages

The carbonation analyzer UC09 is a 100% in line optical sensor able to measure accurately CO2 content of any carbonated beverage, beer, wine or mineral water: the installation can be easily made by means of 1 single Varivent fitting with no need of any bypass or pump.

The equipment is using optical ATR infrared technology specifically developed by Maselli for this application: the new innovative design of the analysis section allows now to withstand both standard and High Temperature applications where the temperature of the CIP exceeds 90°C.

The analyzer does not have any drift in the time so that it does not need any adjustment vs the laboratory: after the initial configuration during start up, the operators in the plant do not have to touch the system anymore.

The measurement is very fast (3 seconds) and it helps the plant operators to control the process.

Due to the optical technology, no moving parts, the equipment is virtually no maintenance reducing drastically the ownership costs in comparison with the traditional pressure / temperature construction.



INFRARED CARBONATION ANALYZER

CO2 FOR THE BEVERAGE AND BEER INDUSTRY

CO2/O2 combined measurement

The carbonation analyzer UC09 may be delivered in combination with the flourescence quencing based oxygen analyzer UG01: the 2 analyzers may be controlled by the Maselli touch screen field panel MP01 capable to handle PLC connection for process alarm and control.

The 2 sensors may be installed in 1 single standard Varivent fitting: being a modular construction, it is possible to start with 1 element adding the second one at a later stage.





mzøi

OPERATING SPECIFICATION

CO2 Measurement

0...6 v/v (0...12 g/l) Measurement range: +/-0.025 v/v (+/-0.05 g/l)Reproducibility: "v/v (Gas/Vol)" or "g/l" Measurement scale:

TECHNICAL FEATURES

-5...+35 °C [23...95 °F] **Product Temperature:**

Line pressure: max 10 bar (145 psi) at 20 °C (68 ° F)

Degree of protetion: IP67 from EN60529 DC 24V ±10%, 10W Power supply:

Digitai interface: RS485 for connection to M8,MP01/02 receivers

Tuchenhagen Varivent N and all Maselli available Line connection:


mounting fittings

Please refer to the technical datasheet for further data.



IBØ8

Beverage Analyzer



In Line - Bx / Diet / CO2

BA06

Beer Analyzer



In line - Alcohol, Plato, Extract, CO2





43122 Parma - Italy - Tel. +39.0521.257411 www.maselli.com







222001290C